


REOTEMP Remote Vapor Actuated Thermometers are manufactured to the highest standards for a wide range of uses and may be fitted into almost any temperature indicating application. These instruments are ideal for remote reading, such as panel installations, with capillary lengths of 1 to 100 feet. Being vapor actuated, they are not subject to indicator error due to ambient temperature variations along the capillary tube system, and will give excellent readings provided the temperature being measured is above or below ambient temperature.



Vapor instruments have progressive graduations, and are best read in the upper 2/3 of the dial range. Many ranges are available between -40°F and $+450^{\circ}\text{F}$, and care should be exercised to select a range that will locate the operating temperatures within the upper 2/3 of the dial range (see ranges on back page.)

To order vapor-configured thermometers, with gas actuation (for higher temperature:)

1. Precede vapor P/N with "G" (e.g. GV20 UR)
2. Choose gas range code from p. 23, table 4
3. Specify SS capillary and bulb (e.g. D05-L2)

Specifications:

Dial Sizes: 2", 2 1/2", 3 1/2", 4 1/2"

Dial: Aluminum with white finish and black markings, other colors available.

Pointer: Standard adjustable.

Movement: Brass with precision gearing.

Bourdon Tube: Phosphor bronze.

Accuracy: Plus or minus one scale division. (upper 2/3 scale)

Case: All stainless steel, except: VA45FL (Aluminum) VA45TB (Phenolic).

Process Connection: Plain Bulb, 1/2" NPT Union, 1/2" NPT sliding union on 12" bendable extension, or Thermowell. NOTE: Thermowells must be used whenever the bulb would be exposed to pressure, fluid velocity, or corrosive media

Window: Polycarbonate, or Glass.

Bulb: Stainless Steel or copper. Bulb O.D. 7/16" (threaded), 3/8" (plain). Bulb lengths vary from 2 1/2" to 9 1/4" depending on capillary length.

Capillary: Copper, copper with bronze braid armor, stainless steel, stainless steel with stainless steel armor. Capillary lengths 1 to 100 feet (standard length 5 feet).

Ranges: Over twenty $^{\circ}\text{F}$ and $^{\circ}\text{F}/^{\circ}\text{C}$ ranges available, from -40° to $+450^{\circ}\text{F}$ (see illustration, back page).

Applications: Control panels, chemical processing, pipelines, food processing, OEM applications, ovens, solar heating, refrigeration, etc.


Filled System Thermometers

Vapor Actuated - How to Order

Model V Vapor Actuated	Case Style & Size (Table 1)	Temperature Range (Table 2)	Capillary & Bulb (Table 3)	Capillary Length (in Ft.) (Table 4)	Process Connection (Table 5)
V	20FR	21	D	05	L2


Table 1 - Case Style

Front Flanged (Panel Mount)




Code	Dial	Case	Lens	Connection Location
20FR	2"	SS	Polycarbonate*	Rear
25FR	2 1/2"	SS	Polycarbonate*	Rear
35FR	3 1/2"	SS	Polycarbonate*	Rear
45FR	4 1/2"	SS	Polycarbonate*	Rear
45FL	4 1/2"	Black Aluminum (hinge ring type)	Glass	Rear

U-Clamp (Panel Mount)





Code	Dial	Case	Lens	Connection Location
20UR	2"	SS	Polycarbonate*	Rear
25UR	2 1/2"	SS	Polycarbonate*	Rear
35UR	3 1/2"	SS	Polycarbonate*	Rear

Rear Flanged (Surface Mount)



Code	Dial	Case	Lens	Connection Location
20RR	2"	SS	Polycarbonate*	Rear
35RR	3 1/2"	SS	Polycarbonate*	Rear
35RB	3 1/2"	SS	Polycarbonate*	Bottom
45RR	4 1/2"	SS	Polycarbonate*	Rear
45RB	4 1/2"	SS	Polycarbonate*	Bottom
45TB	4 1/2"	Phenolic	Glass**	Bottom (Turret Mount)

Other Case Styles



Code	Dial	Case	Lens	Connection Location*
35SB	3 1/2"	SS	Polycarbonate	Adjustable Bracket Mount
45SB	4 1/2"	SS	Polycarbonate	Mount
35DA	3 1/2"	SS	Polycarbonate	"Direct" adj. Mount w/3.4 Cu bulb, 1/2" NPT
45DA	4 1/2"	SS	Polycarbonate	

*Glass lens available, specify "Glass Lens"
**Polycarbonate, lens available, specify "Poly Lens"
*Specify Model & Range Only.
Example: **V45DA-80**

REOTEMP INSTRUMENT CORPORATION

Telephone: (800) 648-7737 FAX (858) 784-0720 • sales@reotemp.com • www.reotemp.com

Table 2 -- Temperature Ranges *Ranges over 350°F come with 316SS Capillary only.

Code	°F Range	Code	°F and °C Ranges
20	-40 TO 60°F	21	-40 TO 60°F & -40 TO 15°C
30	-40 TO 110°F	31	-40 TO 110°F & -40 TO 40°C
32	-20 TO 120°F	33	-20 TO 120°F & -30 TO 50°C
72	0 TO 180°F	73	0 TO 180°F & -20 TO 80°C
49	0 TO 150°F	79	0 TO 150°F & -15 TO 65°C
80	20 TO 220°F	81	20 TO 220°F & 0 TO 105°C
50	40 TO 240°F	51	40 TO 240°F & 0 TO 115°C
56	0 TO 250°F	57	0 TO 250°F & -20 TO 120°C
60	30 TO 300°F	61	30 TO 300°F & 0 TO 150°C
68*	100 TO 350°F	66	100 TO 350°F & 40 TO 175°C
70*	200 TO 450°F	71*	200 TO 450°F & 100 TO 230°C

Table 3 -- Capillary & Bulbs

Code	Capillary & Bulb Material	Capillary Protection
A	Copper	None
C	Copper	Bronze Braid
D	316 SS	None
E	316 SS	S.S. Armor

Table 4 -- Capillary Length


Specify Length in feet.
Standard Length = 5 Ft.
Available Capillary Length: 1-100Ft.
 Note: Capillary Lengths over 5 feet affect bulb length.
 See table at bottom of page.

Table 5 -- Process Connection

Code	Connection Type	Material	
J1	None (Plain Bulb)	Brass - (For Existing Brass Well) 316 SS - (For Existing Stainless Well)	
J2	Jam Nut Only		
J3	Jam Nut Only		
K2	1/2" NPT Union	Brass	
L2	1/2" NPT Union	316 SS	
M2	1/2" NPT Sliding Union on Bendable Extension	316 SS - (Only Avail. with 316 SS Capillary)	
		Brass	
		316 SS	
		1/2 NPT	3/4 NPT
		1/2 NPT	3/4 NPT
For 1-10 ft. Capillary (bulb #1)		12B	13B
For 11-25 ft. Capillary (bulb #2)		22B	23B
For 26-50 ft. Capillary (bulb #3)		32B	33B
For 51-75 ft. Capillary (bulb #4)		42B	43B
For 76-100 ft. Capillary (bulb #5)		52B	53B

Thermowells For Vapor Actuated Bulbs (except M2)

Bulb Configurations



Standard Bulb Dimensions (inches)


CAPILLARY LENGTH	PLAIN BULB		UNION CONNECTION			THERMOWELL			BENDABLE EXT.		
	L	D	U	S	D	U	S	D	L	S	D
1-10 ft. (bulb #1)	2 ¹ / ₂ (1-5ft.) 3 ⁷ / ₁₆ (6-10ft)	3/8	1 ¹³ / ₁₆	2 ³ / ₈	7/16	1 ¹⁵ / ₁₆	2 ¹ / ₂	9/16	2 ¹ / ₂ (1-5ft.) 3 ⁷ / ₁₆ (6-10ft)	3 - 13 4 - 14	3/8
11-25 ft. (bulb #2)	3 ⁷ / ₁₆	3/8	2 ¹ / ₂	3 ¹ / ₄	7/16	2 ⁵ / ₈	3 ³ / ₈	9/16	3 ⁷ / ₁₆	4 - 14	3/8
26-50 ft. (bulb #3)	4 ⁷ / ₈	3/8	4 ¹ / ₂	5 ¹ / ₄	7/16	4 ⁵ / ₈	5 ³ / ₈	9/16	4 ⁷ / ₈	5 - 15	3/8
51-75 ft. (bulb #4)	7 ⁷ / ₈	3/8	6 ¹ / ₂	7 ¹ / ₄	7/16	6 ⁵ / ₈	7 ³ / ₈	9/16	7 ⁷ / ₈	8 - 18	3/8
76-100 ft. (bulb #5)	10 ⁷ / ₈	3/8	8 ¹ / ₂	9 ¹ / ₄	7/16	8 ⁵ / ₈	9 ³ / ₈	9/16	10 ⁷ / ₈	11 - 21	3/8

Filled System Thermometers

Vapor Actuated


Dial Faces

Typical dial faces shown below; complete list shown on page 19.
Operating temperatures should be in upper 2/3 of selected range.



For Temperatures above or below those shown, ask for information on REOTEMP Gas Actuated Thermometers.

Case and Mounting Dimensions (inches)



Dial Sizes	A	B	C	D	E	F	G	H	J
2"	2.94	2.25	2.94	1.25R	2.05	0.98	1.28R	2.3	0.14
2 1/2"	3.69	2.81		1.66R	2.56	1			0.17
3 1/2"	4.75	3.97	4.75	2.16R	3.59	1.41RF .75UC, FF	2.16R	3.69	0.16
4 1/2"	5.88FR 6.31FL		5.88RR, RB 5.83TB	2.69R	4.59FR 47RR, RB, FL	1.41RF .75UC, FF 2.56TB 1.63FL	2.69R	4.69	0.22

REOTEMP INSTRUMENT CORPORATION

Telephone: (800) 648-7737 FAX (858) 784-0720 • sales@reotemp.com • www.reotemp.com